

Contract Line Item Numbers & Salient Characteristics Attachment

Salient Characteristics (SC) Literature Review

Automated Coverslipper Machine

CLIN	Brand	Product Number	Description
0001	Leica	14047839700	Leica CV5030 (1 Basic Instrument)
0002	Leica	149CVTS5015	Leica CV5030-TS5015
0003	Leica	149CVTS5025	Leica CV5030-TS5025

The following SCs pertain to CLINs 0001, 0002, and 0003.

- SC 1** High-throughput glass coverslipper (min 300 slides/hour)
- SC 2** Compact bench top unit (demensions NTE 420 x 600 x 550 mm, 16.5 x 24 x 22 in)
- SC3** Works with coverslips in various sizes from 22-24 mm x 40-60 mm
- SC 4** 100-250 VAC / 50-60 Hz
- SC 5** Broken coverslips can be detected and handled automatically.
- SC 6** Minimum volume of 250-ml glass mounted bottle
- SC 7** Allows for adjustment of mounting media flow volume and in accordance with mounted viscosity
- SC 8** Must be compatible with commercially available types of mounting media (not brand specific)
- SC 9** Wet coverslipping from xylene capability
- SC 10** Dispenser nozzle must be able to rest in xylene-filled receptacle
- SC 11** Permanent fume extraction via activated carbon filter (integrated fume extraction system).
- SC 12** Must be compatible with commercially available slide racks (not brand specific)
- SC 13** Permanent self monitoring function with acoustic and optical instrument status indications
- SC 14** Error codes displayed in the event of malfunctions and other functional errors
- SC 15** Designed and manufactured to conform to the applicable CSA and CE guidelines

--- End ---