

PRODUCT DESCRIPTION

For

NON-EXPENDABLE EQUIPMENT:

WARMING CABINETS



Prepared By:

Strategic Acquisition Center
Department of Veterans Affairs
10300 Spotsylvania Avenue, Suite 400
Fredericksburg, VA 22408

1. SCOPE OF WORK:

The Veterans Health Administration (VHA) Non-Expendable Equipment National Program has identified the Warming Cabinets product line as a candidate for a VA-wide (otherwise referred to as “national”) single Requirements contract award. A warming cabinet stores and warms linens, blankets, and sterile intravenous (IV) and surgical irrigation fluids in a medical environment. Warming cabinets often come in various sizes, and may have one, two or three compartments. They are often used to warm IV and surgical irrigation fluids to reduce the risk of hypothermia in a patient following a surgical procedure. Other environments like spas, dentist offices, and veterinary offices may also utilize blanket warmers. The Contractor must demonstrate the ability to meet all requirements for the solicitation. The objective is to provide Warming Cabinets to be used by clinicians throughout the VA medical centers and facilities. The period of performance is for one (1) 12 month base period with two (2) twelve (12) month option periods.

2. REQUIREMENT

This requirement will be IAW FAR clause 52.211-6, “Brand Name or Equal” which requires that the quoter indicate that each product that is being offered as an “equal” product to the Seris AMSCO® brand of Warming Cabinets. For each equal product, the offeror must include a description reflecting the salient characteristics (SC) and level of quality that will satisfy the salient physical, functional, or performance characteristics of the equal product(s) specified in the solicitation. The quoter must also clearly identify the item by brand name (if any) and make/model number. Finally, the quoter must include descriptive literature, such as illustrations, drawings, or a clear reference to previously furnished descriptive data or information available to the contracting officer, and clearly describe any modifications it plans to make to a product to make it conform to the solicitation requirements.

| CLIN | MFG | Description/Part Number |
|------|--------|---|
| | | SINGLE COMPARTMENT WARMING CABINETS |
| 0001 | Steris | AMSCO Single Compartment Warming Cabinet ; DJ04112033 |
| 0002 | Steris | AMSCO Small Warming Cabinets, Counter Top, Blanket Warmers ; QDJ03 |
| 0003 | Steris | AMSCO Warming Cabinet Glass Door, Stainless Steel, 24D Inch ; DJ060124131 |
| 0004 | Steris | AMSCO Small Warming Cabinets, Counter Top, Blanket Warmers ; QDJ01 |
| 0005 | Steris | AMSCO Single Chamber Blanket Warmer-Counter Top Warming Cabinet: QDJ05 |
| 0006 | Steris | AMSCO Mobile Cart for Single Compartment Warming Cabinet: XS780037WCNC |
| | | DUAL COMPARTMENT WARMING CABINETS |
| 0007 | Steris | AMSCO Dual Chamber Blanket/Fluid Warming Cabinet ; QDJ04 |
| 0008 | Steris | AMSCO Dual Compartment Warming Cabinet ; DJ040124331 |

| | | |
|------|--------|---|
| 0009 | Steris | AMSCO Warming Cabinet Blanket and Fluid, SS, Split Glass Door ; DJ060124331 |
| 0010 | Steris | Replacement Fan Kit 5th Generation ; P413720-635 |
| 0011 | Steris | AMSCO Cabinet Warming Blanket and Fluid DD Glass Double Door ; DJ06012133 |
| 0012 | Steris | AMSCO Upper And lower Heating Chamber Cabinet; DJ06012433113 |
| 0013 | Steris | AMSCO Warming Cab Std Glass Dual 24in 120v: DJ060124331 |

The Department of Veterans Affairs (VA) is seeking vendors who can provide Seris AMSCO® brand of Warming Cabinets as listed above or equal commodities which meet all of the following salient characteristics:

| SC | APPLICABLE CLINs | SALIENT CHARACTERISTICS | METHOD OF EVALUATION |
|-------|-------------------------------------|--|----------------------|
| SC 1 | 0001 | Single chamber size 24.25”H x 30”W x 26.5”D with stainless steel door | Literature Review |
| SC 2 | 0002 | Single chamber size 30”W x 26.5”W x 24.5”D with stainless steel or dual-pane tempered glass | Literature Review |
| SC 3 | 0003 | Single chamber size 24.25”H x 30”W x 26.5” D with dual-pane tempered glass | Literature Review |
| SC 4 | 0004 | Single chamber size 29.75”H x 28”W x 25”D with stainless steel panels | Literature Review |
| SC 5 | 0005 | Single chamber with 24”H x 30”W x 26”D with stainless steel panels | Literature Review |
| SC 6 | 0007 | Dual cabinet overall dimensions of 30”W x 28”D x 75.5”H with stainless steel or dual-pane tempered glass | Literature Review |
| SC 7 | 0008 | Dual cabinet with overall dimensions of 74.75” H x 30” W x 26.5” D with stainless steel door | Literature Review |
| SC 8 | 0009 | Dual cabinet with overall dimensions of 74.75”H x 30”W x 26.5” D with glass door | Literature Review |
| SC 9 | 0011 | Dual cabinet with overall dimensions of 74.75”H x 30”W x 26.5” D with glass door and 3 shelves unit | Literature Review |
| SC 10 | 0012 | Dual cabinet with overall dimensions of 79.1” H x 34.1W x 30.75”D with steel or dual-pane tempered glass | Literature Review |
| SC 11 | 0013 | Dual cabinet with overall dimensions of 74.75” H x 30”W x 26.5””D with steel or dual-pane tempered glass | Literature Review |
| SC 12 | 0001, 0002, 0003, 0004, 0005 | Cabinet must be available in freestanding installations | Literature Review |
| SC 13 | 0007, 0008, 0009, 0011, 0012, 00013 | Cabinet must be available in recessed (built-in) installations | Literature Review |

| | | | |
|-------|---|---|-------------------|
| SC 14 | 0001, 0002, 0003, 0004, 0005, 0007, 0008, 0009, 0011, 0012, 00013 | Cabinet must be distribute heat evenly and efficiently with consistent warmth | Literature Review |
| SC 15 | 0001, 0002, 0003, 0004, 0005, 0007, 0008, 0009, 0011, 0012, 00013 | Cabinet must offer digital control technology | Literature Review |
| SC 16 | 0001, 0002, 0003, 0004, 0005, 0007, 0008, 0009, 0011, 0012, 00013 | Cabinet must offer independently controlled chambers | Literature Review |
| SC 17 | 0001, 0002, 0003, 0004, 0005, 0007, 0008, 0009, 0011, 0012, 00013 | Cabinet must offer adjustable shelf design | Literature Review |
| SC 18 | 0001, 0002, 0003, 0004, 0005, 0007, 0008, 0009, 0011, 0012, 00013 | Average temperature range 90 degrees Fahrenheit to 160 degrees Fahrenheit | Literature Review |
| SC 19 | 0001, 0002, 0003, 0004, 0005, 0007, 0008, 0009, 0011, 0012, 00013 | Cabinet must offer lock-out for consistency and control | Literature Review |
| SC 20 | 0001, 0002, 0003, 0004, 0005, 0007, 0008, 0009, 0011, 0012, 00013 | The units meet AORN Recommended Practices for a Safe Environment of Care, including a design that is built for warming IV solutions (RP VIII.b.3) | Literature Review |
| SC 21 | 0006 | Mobile cart designed to hold 24" single compartment Warming Cabinets with locking casters | Literature Review |
| SC 22 | 0010 | Fan kit must be compatible for the upper and lower compartments for AMSCO blanket warmer for proper circulation | Literature Review |